

MinimoAutofold

The number one choice for maximum convenience and transportability.

The compact Minimo Autofold has all the benefits of the Minimo Plus but delivers automated powered folding in one simple movement.

The finest in its class, the Autofold is simple to operate. By swiping the control fob and pressing the foot pedal to start the automated folding, the need for bending down is eliminated to maximise convenience. But this is also the solution for you if you're after something stylish as well as compact. Easily navigate the sleek control panel, sit in comfort on the mesh-style padded seat and be easily seen with the LED front light.

This high specification 4mph scooter has a traditional four-wheel configuration for extra stability, a tight turning radius for negotiating corners and features pneumatic tyres for a smooth ride. What's more, the Autofold is ideal for transporting in the car and taking on the plane thanks to its lightweight lithium battery and compact frame.

- Travel up to 4mph for a range up to 10 miles (16km)
- Pneumatic tyres and four-wheel configuration for stability
- Maximum user weight of 18 stone (115kg)
- Stylish design based on the Minimo family of scooters
- Simple control panel with LED battery gauge
- Removable seat and battery for easy transportation
- Safety sensor to control cornering speeds

Full details on the website www.tgamobility.co.uk



"It is wonderful. It is the best mobility scooter I have ever had. So reliable, so well made, amazing. I couldn't be more pleased."

Mrs De Castro.

MinimoAutofold



Available in Titanium
Silver Metallic only

Specification and comparison table on Page 82-83

Maximum Speed (up to)	Maximum Weight	Range (up to)	Vehicle Class
4mph	18 stone	10 miles	2 - pavement scooter



Instead of inserting a key into the ignition, swiping the remote fob 'wakes up' the control panel display



Lightweight battery can be lifted out and charged separately and is airline compliant.



Large, LED front and rear lights offer more visibility for other road users. Pneumatic tyres provide a smooth ride




By pressing 'Autofold' button on the handlebar and then the foot pedal, the Autofold will start folding



From its standing position, the Autofold automatically folds into a compact unit

Options and Accessories



Underseat bag



Front basket



Easy lifting handle



Stick holder